



PlugTail® Industrial Extra Heavy-Duty Spec Grade Receptacles, 15A, 125A

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007860177	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC

Dimensions

Product Width US	1.625 in	Product Depth US	0.866 in
------------------	----------	------------------	----------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Three	Number of Wires	3
-------	-------	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG
-----------	-------------