



Pass and Seymour

Discontinued - PlugTail® Extra Heavy Duty Hospital Grade Illuminated Receptacles, 15A, 125V, Red
Part No. PT8200ILRED



PlugTail® Extra Heavy-Duty Hospital Grade Illuminated Duplex Receptacle, 15amp 125volt, Red

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007238655	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Three	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		