



Pass and Seymour
PlugTail® 20A 125V Heavy Duty Hospital-Grade Compact Duplex Receptacle, Ivory
Part No. PT8300HI



PlugTail® Heavy-Duty Compact Design Hospital-Grade Duplex Receptacle PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Large brass contacts snugly terminate on device blade terminals.

Wire Size: #12 AWG THHN

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	CSA Listed, CUL, FSUL, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	12 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		
