



Pass and Seymour
PlugTail® 20A 125V Heavy Duty Hospital-Grade Compact Duplex Receptacle, Light Almond
Part No. PT8300HLA



PlugTail® Heavy-Duty Compact Design Hospital-Grade Duplex Receptacle PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Large brass contacts snugly terminate on device blade terminals.

Wire Size: #12 AWG THHN

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007091410	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial, Hospital Grade
Standard	CSA Lsied, CUL, FSUL, UL Listed, FEDSPEC	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Phase	Single
Connection	PlugTail	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	12 AWG
Indoor/Outdoor	Indoor	Environmental Conditions	UL94 V2
