



Pass and Seymour
PlugTail® 20A 125V Extra Heavy Duty Hospital-Grade Duplex Receptacle, Ivory
Part No. PT8300I



PlugTail® Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V
PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Large brass contacts snugly terminate on device blade terminals.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|----------------|-------------------|--------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Commercial, Indoor |

| | | | |
|---------------------------------------|------------|------------------|-------------|
| Application Sector | Commercial | Standard | UL 498 |
| Type | Outlet | | |
| Dimensions | | | |
| Product Width US | 1.625 in | Product Depth US | 0.856 in |
| Product Height US | 2.75 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | 140596 | cULus Listed | Yes |
| Technical Information | | | |
| Amperage | 20 A | Number of Poles | Double Pole |
| Wire Size | 4 AWG | Indoor/Outdoor | Indoor |
| Voltage | 125.0 V | | |