



Pass and Seymour
PlugTail® Hospital Grade Extra Heavy Duty Surge Protective Duplex Receptacle, Brown
Part No. PT8300SP

PlugTail information, visit our PlugTail Headquarters.



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007019858	Country Of Origin	China
Number of Receptacles	2	Features	Audible Alarm, Brass Mounting Strap, Indicator Lights, Surge Protection
Outlet Type	Hospital Grade, Surge Protected	Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	No	Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL

Warranty Type	1-Year Limited Warranty
---------------	-------------------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Connection Location	Back Only
Phase	Single	Connection	Built-in Connector
Class	IG	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Operating Temperature	-40°-60°C	Wire Connection Type	PlugTail
Type of Indicators	Audible Alarm, LED	Voltage	125.0 V
Environmental Conditions	UL94 V2		