



PlugTail information, visit our PlugTail Headquarters.



Features & Benefits

| | |
|---|--|
| .036 inch thick, brass, triple-wipe power contacts for lasting retention. | Plated steel wrap strap design for maximum durability and corrosion resistance. |
| No exposed terminals create a finger safe application before, during, and after installation. | Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. |
| Crimped and welded contacts. | Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. |
| Large brass contacts snugly terminate on device blade terminals. | Pre-stripped connector leads fasten to conductors, easier than standard pigtails. |
| Auto-ground clip assures positive ground. | For covering patents, see www.legrand.us/patents . |

Specifications

General Info

| | | | |
|-------------------|--|--------------------|-------------------------|
| Product Line | Pass & Seymour | UPC Number | 785007019728 |
| Country Of Origin | China | Application Sector | Commercial, Residential |
| Standard | CSA Listed, cUL, UL Listed, RoHS, FSUL | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|--------------------|--------------------|--------------------------|--------------------|
| Phase | Single | Connection | Built-in Connector |
| Class | IG | Amperage | 15 A |
| Type of Indicators | Audible Alarm, LED | Environmental Conditions | UL94 V2 |