



Pass and Seymour  
**PlugTail® Connectors, Right Angle with Ground Screw, Solid, 6"**  
Part No. PTR6SOLG



PlugTail® Connectors, Right Angle with Ground Screw, Solid, 6-inch

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Large brass contacts snugly terminate on device blade terminals.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007242751
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus UL498		

### Dimensions

Product Length US	6.0 in
-------------------	--------

---

Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
Temperature Rating	-40° - 60° C	Number of Poles	Double Pole
Wire Size	12 AWG	Environmental Conditions	Flammability: UL94 V2

---