



Pass and Seymour  
North American Compliant PlugTail® Connectors, Right Angle, Solid, 6-in  
Part No. PTR6SOLNA



North American Compliant PlugTail® Connectors Right Angle Solid 6-inch.

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.	Large brass contacts snugly terminate on device blade terminals.
Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.	Available in any wire length up to 25 inches, use Configurable Solutions to order.
North American Compliant	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only	

## Specifications

General Info			
Product Line	Pass & Seymour	UPC Number	785007008289
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus UL498		
Dimensions			
Product Length US	6.0 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
Temperature Rating	-40° - 60° C	Number of Poles	Double Pole
Wire Size	12 AWG	Environmental Conditions	Flammability: UL94 V2

---