



Pass and Seymour
PlugTail® Connector in Orange, Right Angle, Solid, 6-in XHHW-2 Wire
Part No. PTR6SOLOR

PlugTail® Connectors, Right Angle, Solid, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Orange connector makes identifying isolated ground circuits easier.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Distinguished orange connector head to help identify isolated ground circuits during rough in or device replacement.

PlugTail™ Orange Connector: #12 AWG, THHN, copper conductor, 6 - in leads, stripped, solid, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Country Of Origin	Mexico	Construction	Injection Molded Plastic
Features	Plug-In, Right Angle	Package Quantity	1
Application Sector	Commercial	Standard	RoHS, cULus
Warranty Type	1-Year		

Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Wire Size	12 AWG	Indoor/Outdoor	Indoor
Connection Type	Wired	Environmental Conditions	0 to 95% (relative humidity, non-condensing)
