



Pass and Seymour  
**PlugTail® Connectors, Right Angle, Stranded, XHHW Black Blue, 6"**  
Part No. PTR6STRXBB



PlugTail® Connectors, Right Angle, Stranded, XHHW Black Blue, 6-inch

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

NAFTA-Compliant

Ideal for applications with low leakage current requirements

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Large brass contacts snugly terminate on device blade terminals.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

Uses #12 AWG stranded XHHW wire

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
--------------	----------------	-------------------	--------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----