



Pass and Seymour
PlugTail® Switch, Right Angle with IDEAL Connector, 3-Wire, 6-inch Stranded THHN12
Part No. PTS6STR3BP



PlugTail® Switch Right Angle with WAGO Connector 3-Wire, 6-inch Stranded THHN12

Features & Benefits

All PlugTail: Connectors are available in any wire length up to 25 inches

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

For covering patents, see www.legrand.us/patents.

Large crimped and welded brass contacts

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007001167
Country Of Origin	Mexico		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----