



Pass and Seymour  
**PlugTail® Switch, Right Angle Connector, 3-Wire, Stranded, 6-in XHHW-2 Wire**  
Part No. PTS6STR3X2



PlugTail® Switch, Right Angle Connector, 3-Wire, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each switch. Utilizes XHHW-2 wire.

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Utilizes XHHW-2 wire which is a thermoset insulated with XLPE (cross-linked Polyethylene).

Substantially higher insulation resistance than THHN wire and does not have PVC in insulation.

Ideal for projects requesting that products be free of any components on Red List.

Wire temperature rated 90°C Wet/Dry.

PlugTail™ Connector: #12 AWG, XHHW - 2, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Switches only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Construction	Injection Molded Plastic
Features	Plug-In, Right Angle	Package Quantity	1
Application Sector	Commercial	Standard	RoHS, cULus
Warranty Type	1-Year		

### Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

---

## Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

## Technical Information

---

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

---

Connection Type	Plugtail, Wired	Environmental Conditions	0 to 95% (relative humidity, non-condensing)
-----------------	-----------------	--------------------------	--

---