



Pass and Seymour
PlugTail® Switch Right Angle with IDEAL Connector, 4-Wire, Stranded, 6-in XHHW-2 Wire
Part No. PTS6STR4BPX2



PlugTail® Switch, Right Angle with IDEAL Connector, 4-Wire, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each switch. Utilizes XHHW-2 wire.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Utilizes XHHW-2 wire which is a thermoset insulated with XLPE (cross-linked Polyethylene).

Substantially higher insulation resistance than THHN wire and does not have PVC in insulation.

Wire temperature rated 90°C Wet/Dry.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Ideal connectors for fast and secure wire termination.

Ideal for projects requesting that products be free of any components on Red List.

PlugTail™ Connector: #12 AWG, XHHW - 2, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Switches only

Specifications

General Info

| | | | |
|--------------------|----------------------|------------------|--------------------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | Mexico | Construction | Injection Molded Plastic |
| Features | Plug-In, Right Angle | Package Quantity | 1 |
| Application Sector | Commercial | Standard | RoHS, cULus |
| Warranty Type | 1-Year | | |

Dimensions

| | | | |
|-------------------|--------|-------------------|---------|
| Product Width US | 1.0 in | Product Weight US | 0.06 lb |
| Product Height US | 1.0 in | Product Length US | 6.0 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

| | | | |
|-----------------|-----------------|--------------------------|--|
| Wire Size | 12 AWG | Indoor/Outdoor | Indoor |
| Connection Type | Plugtail, Wired | Environmental Conditions | 0 to 95% (relative humidity, non-condensing) |
