



PlugTail® Tamper-Resistant Decorator Spec Grade Receptacle, 15A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.	No exposed terminals create a finger safe application before, during, and after installation.
Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.	Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
Crimped and welded contacts.	Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.	Auto-ground clip assures positive ground.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007001341
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Standard	UL 498, FEDSPEC	Warranty Type	1-Year Limited Warranty
Type	Outlet		

### Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
Product Height US	2.75 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus Listed                      Yes

---

Technical Information

---

Is Tamper-Resistant              Yes                                      Phase                                      Three

---

Amperage                              15 A                                      Number of Poles                      Double Pole

---

Indoor/Outdoor                      Indoor

---