



Pass and Seymour
PlugTail® 20A 125V Hospital-Grade Tamper-Resistant Decorator Duplex Receptacle, White
Part No. PTTR26362HGW



PlugTail® Tamper-Resistant Hospital Grade Decorator Receptacle, 20A 125V.
PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects	.036 inch thick, brass, triple-wipe power contacts for lasting retention.
Plated steel wrap strap design for maximum durability and corrosion resistance.	No exposed terminals create a finger safe application before, during, and after installation.
Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.	Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
Auto-ground clip assures positive ground.	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only	

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007008609
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Hospital Grade

Standard	FEDSPEC	Type	Outlet
Dimensions			
Product Width US	1.5 in	Product Depth US	0.875 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Is Tamper-Resistant	Yes	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor