



PlugTail® Tamper-Resistant Decorator Spec Grade Receptacle, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

---

Product Width US	1.5 in	Product Depth US	0.875 in
------------------	--------	------------------	----------

---

Product Height US	2.75 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	Amperage	20 A
---------------------	-----	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

Voltage	125.0 V
---------	---------

---