



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Dual mechanical shutter system to help prevent insertion of foreign objects (TR models).

Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.

Auto-ground clip assures positive ground.

Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Wire Size: #12 AWG THHN

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus, UL Listed		

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Phase	Single	Connection	PlugTail
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	12 AWG	Voltage	125.0 V
Environmental Conditions	UL94 V2		
