



PlugTail® Tamper-Resistant Split Circuit Decorator Spec Grade Receptacle, 20A, 125A

Features & Benefits

| | |
|--|---|
| .036 inch thick, brass, triple-wipe power contacts for lasting retention. | Plated steel wrap strap design for maximum durability and corrosion resistance. |
| No exposed terminals create a finger safe application before, during, and after installation. | Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. |
| Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. | Crimped and welded contacts. |
| Large brass contacts snugly terminate on device blade terminals. | Pre-stripped connector leads fasten to conductors, easier than standard pigtails. |
| Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications. | Auto-ground clip assures positive ground. |
| For covering patents, see www.legrand.us/patents . | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here . |

Specifications

General Info

| | | | |
|-------------------|-----------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | UPC Number | 785007001914 |
| Country Of Origin | Mexico | Application Sector | Commercial, Residential |
| Standard | UL 498, FEDSPEC | | |

Dimensions

| | | | |
|-------------------|--------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.875 in |
| Product Height US | 2.6 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------------|------|-------|-------|
| cULus Listed | Yes | | |
| Technical Information | | | |
| Is Tamper-Resistant | Yes | Phase | Three |
| Amperage | 20 A | | |