



Pass and Seymour
PlugTail® 15A 125V Tamper Resistant Heavy-Duty Spec Grade Single Receptacles, White
Part No. PTTR5261W



Plugtail Heavy-Duty Spec Grade Single Receptacles with Side and Back Wire install 5x faster than conventional wiring devices.

In the world of commercial wiring device installation, it's all about flexibility. For years now, PlugTail® electrical wiring devices have been providing that flexibility in commercial buildings everywhere. Easy to install, change out and upgrade, PlugTail allows you to continuously reconfigure to meet a building's electrical requirements as the space transforms – without the time and expense of rewiring. It's a cost-effective, code-compliant, proven way to keep your customers connected to the future, while securing your reputation as a forward-thinking electrical contractor.

Specifications

General Info

| | | | |
|-----------------------|---------------------------|-------------------------|-------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | |
| Color | White | Finish | Glossy |
| Country Of Origin | Mexico | Receptacle Type | Straight Blade |
| Number of Receptacles | 1 | Outlet Type | Tamper-Resistant |
| Package Quantity | 1 | Application Sector | Commercial |
| Standard | UL UL498, CSA No.C22.2 | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet, Plug Tail, Single | | |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 1.546 in | Product Depth US | 1.9 in |
| Product Height US | 4.185 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|--------|----------|---------|
| Is Tamper-Resistant | Yes | Amperage | 15 A |
| Indoor/Outdoor | Indoor | Voltage | 125.0 V |

Environmental Conditions 95% (relative humidity, non-
condensing)
