



Pass and Seymour
PlugTail® 20A 125V Tamper Resistant Heavy-Duty Spec Grade Single Receptacles, Ivory
Part No. PTTR5361I



Plugtail Heavy-Duty Spec Grade Single Receptacles with Side and Back Wire install 5x faster than conventional wiring devices.

In the world of commercial wiring device installation, it's all about flexibility. For years now, PlugTail® electrical wiring devices have been providing that flexibility in commercial buildings everywhere. Easy to install, change out and upgrade, PlugTail allows you to continuously reconfigure to meet a building's electrical requirements as the space transforms – without the time and expense of rewiring. It's a cost-effective, code-compliant, proven way to keep your customers connected to the future, while securing your reputation as a forward-thinking electrical contractor.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Glossy	UPC Number	785007442045
Country Of Origin	Mexico	Receptacle Type	Straight Blade
Number of Receptacles	1	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Standard	UL UL498, CSA No.C22.2, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet, Plug Tail, Single

Dimensions

Product Width US	1.546 in	Product Depth US	1.9 in
Product Height US	4.185 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
Indoor/Outdoor	Indoor	Environmental Conditions	95% (relative humidity, non-condensing)