



PlugTail information, visit our PlugTail Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.



## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                        |                   |  |
|--------------------|------------------------|-------------------|--|
| Product Line       | Pass & Seymour         | Country Of Origin | China                                  |
| Application Sector | Residential/Commercial | Standard          | CSA Listed, cUL, UL Listed, RoHS, FSUL |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

---

|            |                    |                          |                    |
|------------|--------------------|--------------------------|--------------------|
| Phase      | Single             | Frequency Rating         | 60 Hz              |
| Connection | Built-In Connector | Class                    | IG                 |
| Amperage   | 15 A               | Type of Indicators       | LED, Audible Alarm |
| Voltage    | 125.0 V            | Environmental Conditions | UL94 V2            |

---