



Pass and Seymour  
**PlugTail® Commercial Passive Infrared (PIR) Wall Switch Sensor, Ivory**  
Part No. PTWSP250I



Commercial Occupancy Sensor (PIR) PlugTail Automatic Wall Switch with 3 Wire Technology. Compact decorator design, shallow 1" back body, positive detection indicator with no minimum load requirement. Available in Ivory, White, Gray and Light Almond.

For detailed PlugTail information, visit our [PlugTail Headquarters](#).

## Features & Benefits

Detection Signature Analysis provides high immunity to RFI and EMI.

Integrated light level sensor works from 10 to 150 footcandles.

Compatible with all electronic and magnetic ballasts, PL lamp ballasts, compact fluorescent.

Adjustable time delay of 30 seconds to 30 minutes.

Dual 120/277VAC operation, Adjustable sensitivity from 20% to 100%, 180 degree coverage of up to 900 sq. ft.

Patented voltage drop protection and zero crossing circuitry.

No exposed terminals create a fingersafe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	WS-301-I
Color	Ivory	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Standard	CSA Listed, cULus, UL Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Target Size	180 deg	Response Frequency	60 Hz
Sensor Type	Occupancy	Sensing Range	900 sq ft
Sensitivity	60Hz	Load	120/277VAC
Environmental Conditions	Indoor Use Only		