



The PW-103N passive infrared (PIR) multi-way wall switch sensor can turn lights OFF and ON based on occupancy. It provides high sensitivity to small and large movements, appealing aesthetics, a field selectable nightlight and a variety of features.

## Features & Benefits

|                                                                                                              |                                                                                                                                                      |
|--------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Detection Signature Processing eliminates false triggers and provides immunity to RFI and EMI                | Defaults to Manual-ON operation for maximum energy savings                                                                                           |
| Vandal resistant lens combines precise coverage with durability                                              | In automatic mode, sensor returns automatically to Auto-ON after lights are turned off manually; ideal for presentations                             |
| Choice of Manual-ON or Auto-ON operation                                                                     | Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds |
| Selectable audible and/or visual alerts for impending shutoff                                                | 2-wire and 3-wire models available for applications with or without neutral wire                                                                     |
| High sensitivity and dense coverage for exceptional performance                                              | Color-matched lens and low profile for appealing design                                                                                              |
| Optional nightlight with choice of three colors and two light levels                                         | Allows multi-way control from one of up to four control locations                                                                                    |
| Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience | High sensitivity and dense coverage for exceptional performance                                                                                      |
| Optional nightlight with choice of three colors and two light levels                                         | Color-matched lens and low profile for appealing design                                                                                              |
| Allows multi-way control from one of up to four control locations                                            | Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience                                         |
| Defaults to Manual-ON operation for maximum energy savings                                                   |                                                                                                                                                      |

## Specifications

### General Info

|                               |                                                 |                         |                                          |
|-------------------------------|-------------------------------------------------|-------------------------|------------------------------------------|
| Product Line                  | Wattstopper                                     | Replaced by Part Number | RS-150BA-N-LA                            |
| Color                         | Light Almond                                    | UPC Number              | 754182928606                             |
| Country Of Origin             | China                                           | Features                | IR (Infrared), Motion Sensor, Nightlight |
| Switch Type                   | Motion Sensor                                   | Application Sector      | Commercial                               |
| Warranty Type                 | 5-Year                                          |                         |                                          |
| Dimensions                    |                                                 |                         |                                          |
| Product Width US              | 2.0 in                                          | Product Weight US       | 0.4 lb                                   |
| Product Volume US             | 27.84 cu in                                     | Product Depth US        | 4.5 in                                   |
| Product Height US             | 2.25 in                                         |                         |                                          |
| Additional Information        |                                                 |                         |                                          |
| Product Environmental Profile | Yes                                             |                         |                                          |
| Technical Information         |                                                 |                         |                                          |
| Response Frequency            | 50/60 Hz                                        | Sensor Type             | Occupancy                                |
| Number of Buttons             | 1                                               | Amperage                | 4.3 A                                    |
| Indicator                     | LED Light                                       | Wattage                 | 1200 W                                   |
| Sensing Range                 | Major motion 35 x 30 ft,Minor motion 20 x 15 ft | Voltage                 | 120/277 V                                |
| Connection Type               | Wired                                           |                         |                                          |