



The PW-301 passive infrared (PIR) wall switch sensor can turn lights OFF and ON based on occupancy.

Features & Benefits

Color-matched lens and low profile for appealing design

120/240/277 VAC and 347 VAC models

High sensitivity and dense coverage for exceptional performance

Optional neutral connection with break off tab to expose neutral terminals

Allows multi-way control from one of up to four control locations

Defaults to Manual-ON operation for maximum energy savings

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	754182935246
Country Of Origin	China	Features	IR (Infrared), Motion Sensor
Switch Type	Motion Sensor	Application Sector	Commercial
Type	Switch		

Dimensions

Product Width US	1.75 in	Product Depth US	1.81 in
Product Height US	2.73 in	Product Length US	2.73 in

Technical Information

Seismic Tested	No	Response Frequency	60 Hz
Sensor Type	Occupancy	Number of Buttons	1
Number of Poles	Multi-Location	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Wattage	1200 W	Mounting Type	Box
Voltage	120/277 V	Connection Type	Wired