Ortronics

25FT Blue PowerWise Cat5E solid cord Plenum double ended

Part No. PW5EP25DB-06

PWC5E PowerWise Cat5E UTP solid 22 awg conductor plenum, double ended 25ft, blue

Features & Benefits

Each cord is factory tested: Ensures every cord shipped meets Category 5e component specifications

Larger 22 awg conductors: Support higher power levels with less loss

Premium plug qualified for 22 awg horizontal cable patch cable: Protects performance integrity through the plug termination

Snagless plug design: Protects plugs when pulling through cable managers or pathways

Compatible with both T568A and T568B wiring: Provides universal wiring ability

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875960713	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	ANSI/TIA-568.E-2;ISO/IEC 11801-1;RoHS
Warranty Type	5-Year	Type	Copper Patch Cord

Dimensions

Product Length US	25.0 FT	Cable Length	25 ft

Additional Information

RoHS Compliant	Yes

Technical Information

Operating Temperature Min	-10 °C	Category Performance Application	Cat5e
Compatibility	RJ-45	Wire Gauge	24 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Plenum Rated	Bend Radius	0.94 in
Shielded/Unshielded Cable	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Solid	Operating Temperature Max	60 °C
Cable Type	Non-Booted	Jacket Rating	CMP Rated
Cable Diameter	0.235 in	Braid	Non-braided Wiring
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male
Operating Temperature	-10°-60°C	Operating Humidity	0-90% RH (Non-Condensing)
Conductor Material	Copper	Voltage	300.0 V
Connectivity Footprint	PowerWise	Storage Temperature	-40° - 60° C