



Ortronics  
**PowerWise Cat5E solid cord Riser PVC, double ended 10ft, blue**  
Part No. PW5ER10DB-06



PWC5E PowerWise Cat5E UTP solid 22 awg conductor riser, double ended 10ft, blue

## Features & Benefits

- Each cord is factory tested: Ensures every cord shipped meets Category 5e component specifications
- Larger 22 awg conductors: Support higher power levels with less loss
- Premium plug qualified for 22 awg horizontal cable patch cable: Protects performance integrity through the plug termination
- Snagless plug design: Protects plugs when pulling through cable managers or pathways
- Compatible with both T568A and T568B wiring: Provides universal wiring ability

## Specifications

### General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875961833	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Copper Patch Cord		

### Dimensions

Product Length US	10.0 FT	Cable Length	10 ft
-------------------	---------	--------------	-------

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
Category Performance Rating	Cat5e	Wire Gauge	22 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 µ in Gold
Jacket Application	Riser Rated	Bend Radius	0.94 in
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Solid	Operating Temperature Max	60 °C
Jacket Rating	CMR Rated	Cable Diameter	0.235 in
Braid	Non-braided Wiring	Operating Temperature	-10°-60°C
Operating Humidity	0-90% RH (Non-Condensing)	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C