



Cisco QSFP-100G-LR4-S Compatible 100GBase-LR4 QSFP28 Transceiver (SMF, 1295nm-1309nm, 10km, LC Duplex, DDM, C-Temp)



## Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875078265
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

### Dimensions

Product Width US	18.35 mm	Product Depth US	125.35 mm
Product Height US	8.5 mm		

### Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	0 °C
Operating Temperature Max	70 °C	Connector Type	LC Duplex
Form Factor	QSFP28		