



Juniper Networks QSFP4X10GESR Compatible 40GBase-SR4 QSFP+ Transceiver (MMF, 850nm, 150m, MPO/MTP, DDM, C-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.	99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.	98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.	

Specifications

General Info

Product Line	Ortronics	UPC Number	662875077213
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	18.35 mm	Product Depth US	70.9 mm
Product Height US	8.5 mm		

Technical Information

Fiber Optic Cable Type	Multimode	Operating Temperature Min	0 °C
Operating Temperature Max	70 °C	Connector Type	MPO
Wavelength	850 nm		