



Six rear outlets, lighted switch, 15A. 6' [1.8m] cord. Sentrex high performance surge protection.

## Features & Benefits

Six rear outlets, lighted switch, 15A. 15' [4.6m] cord. Sentrex high performance surge protection.

## Specifications

### General Info

Product Line	Wiremold	Color	Black
UPC Number	786776100815	Country Of Origin	Mexico
Product Series	Sentrex	Number of Receptacles	6
Features	Surge Protection	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421: Guide XBYS2, XUHT2, VZCA10	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

### Dimensions

Product Width US	19.0 in	Product Weight US	3.5 lb
Product Height US	2.57 in	Product Length US	1.75 in
Receptacle Spacing	1.5 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Phase	Three Stage	Cord Length	6 ft
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	56000 Amps [32000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Wiring Method	Cord-ended
NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Rack Mounting
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V		