



Complete with one-piece finish flange and conduit assembly with one 3/4" and two 1/2" trade size conduit adapters and closure plugs. Colors available in painted gray (GY), painted black (BK), brushed aluminum (AL), and plated brass (BS). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC7AFFTC Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

Complete with one-piece finish flange and conduit assembly with one 3/4" and two 1/2" trade size conduit adapters and closure plugs	Colors available in painted gray (GY), painted black (BK), brushed aluminum (AL), and plated brass (BS)
NOTE: Assembled with scrub water gasket	For use on tile or carpet floors
RC7AFFTC Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole	Floor covering thickness 1/8" minimum
Floor covering thickness 1/8" minimum	

Specifications

General Info

Product Line	Wiremold	UPC Number	786564132028
Country Of Origin	Mexico	Construction	Assembled
Cover Style	Flush, Furniture Feed	Number of Knockouts	2
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru

Dimensions

Product Weight US	6.71 lb	Product Height US	16.5 in
-------------------	---------	-------------------	---------

Cubic Capacity	24.5 in ³	Core Hole Size	3 in
Knockout Size	1/2 in, 3/4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Floor Type	Carpet, Tile, Wood	Fire Rating	2 hr
Cable Entry	knockout		