




Wiremold
RC7AM2TC Assembled Furniture Feed Poke-Thru Device
Part No. RC7AM2TCGY



2" trade size conduit stem, complete with one 3/4" trade size conduit and two 1/2" trade size adapters and closure plugs. Finish flange/cover assembly available in painted gray (GY), black (BK), brushed plated brass (BS), and brushed aluminum (AL). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC9AM2TC Series Poke-Thru Devices require a 3" (76mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

2" trade size conduit stem, complete with one 3/4" trade size conduit and two 1/2" trade size adapters and closure plugs

Finish flange/cover assembly available in painted gray (GY), black (BK), brushed plated brass (BS), and brushed aluminum (AL)

NOTE: Assembled with scrub water gasket

For use on tile or carpet floors

RC9AM2TC Series Poke-Thru Devices require a 3" (76mm) diameter hole

Floor covering thickness 1/8" minimum

Floor covering thickness 1/8" minimum

Specifications

General Info

Product Line	Wiremold	Color	Gray
UPC Number	786564008712	Country Of Origin	Mexico
Construction	Assembled	Cover Style	Furniture Feed
Number of Knockouts	1	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Poke-Thru		

Dimensions

Product Weight US	4.0 lb	Core Hole Size	3 in
Knockout Size	2 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Floor Type	Carpet, Tile	Service Capacity	Dual
Fire Rating	2 hr	Cable Entry	CONDUIT