



radiant Collection  
radiant® Two Single Pole/3-Way Switches, Black  
Part No. RCD33BK



Control two separate lights or devices from a single location with this combination switch. Both switches feature installation flexibility, usable for single-pole or 3-way applications. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

## Features & Benefits

Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection.

Features durable, high-impact resistant thermoplastic construction.

Designed to install easily with a narrower back body and captivated mounting screws.

Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Satin	UPC Number	785007054934
Country Of Origin	China	Material	Thermoplastic
Features	Combination, Decorator Style, Locator Light	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential
Wall Plate Included	No	Standard	cULus, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Switch

---

## Dimensions

---

Product Width US	1.29 in	Product Depth US	1.59 in
------------------	---------	------------------	---------

---

Product Height US	3.81 in
-------------------	---------

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E140597	cULus Listed	Yes
---------------------	---------	--------------	-----

---

## Technical Information

---

Load Rating	15 A @ 120/125 VAC	Operating Cycles	50000
-------------	--------------------	------------------	-------

---

Connection Location	Back and Side	Terminal Accommodation	#14 AWG - #12 AWG
---------------------	---------------	------------------------	-------------------

---

Number of Gangs	1	Throw Type	Single Throw
-----------------	---	------------	--------------

---

Amperage	15 A	Number of Poles	3-Way, Single Pole
----------	------	-----------------	--------------------

---

Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
-----------------------	-----	----------------	--------

---

Mounting Type	Wall Box	Location Rating	Dry
---------------	----------	-----------------	-----

---

Wire Connection Type	Push Wire, Wire Terminal	Voltage	120 VAC, 125 VAC
----------------------	--------------------------	---------	------------------

---

Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Environmental Conditions	UL94 V2
-----------	--	--------------------------	---------

---