



radiant Collection
radiant® Two Single Pole/3-Way Switches, Nickel
Part No. RCD33NICC6



Control two separate lights or devices from a single location with this combination switch. Both switches feature installation flexibility, usable for single-pole or 3-way applications. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection. Features durable, high-impact resistant thermoplastic construction.

Designed to install easily with a narrower back body and captivated mounting screws. Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.

More color options available to fit any style, including finishes to match current hardware and lighting trends. Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
Finish	Metallic	UPC Number	785007054996
Country Of Origin	China	Features	Combination, Locator Light
Switch Type	Push	Number of Switches	2
Application Sector	Residential	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
------------------	---------	------------------	---------

Product Height US	3.81 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Contact Rating	15 Amp, 120/125 VAC	Number of Gangs	1
Amperage	15 A	Number of Poles	3-Way, Single Pole
Wire Size	#14 - #10 AWG	Mounting Type	Box
Voltage	120.0 V		