



Ortronics
28awg Reduced diameter C6A/10G channel cord Yellow 9FT
Part No. RDC61009-04

RDC610 Modular Patch Cord, yellow, 9', reduced diameter, 28 AWG, cat6a channel four-pair UTP stranded PVC/CM.



Features & Benefits

- Each cord is 100% factory tested: Ensures every cord shipped support Category 6a channel specifications.
- Reduced cable diameter: Tighter bend radiuses & occupy less cable management space supporting more airflow
- Premium plug designed for reduced OD 28AWG patch cable: Protects performance through the plug termination
- Snagless plug design: Protects plugs when routing through cable managers or pathways.
- Premium 28AWG conductor cordage: Reliable performance and durable cord life.
- Backwards compatible to Category 6, and 5e: Supports lower category installations and components.
- Improved cable flexibility: Supports simple routing and cable management

Specifications

General Info

Product Line	Ortronics	UPC Number	662875854203
Country Of Origin	Mexico	Application Sector	Commercial, Industrial
Standard	FCC	Type	Reduced Diameter Patch Cords

Dimensions

Product Length US	9.0 FT
-------------------	--------

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Category	Performance Rating	Cat6a
----------	--------------------	-------
