




Wiremold RFBA 2-Gang Shallow Floor Box Part No. RFBA2R25



Your go-to floor box just got better. Resource RFB Series Floor Boxes are designed for maximum efficiency throughout an entire building, bringing versatile recessed activations for power and data services to open space areas or directly to workstations. No matter what size you choose, components and accessories work across the entire line interchangeably. Simply mix-and-match as needed for your project. Improved wire and cable routing makes wire pulling much easier in adjacent compartments and around corners. Available in 2-, 4-, 6- and 10-gang models with a variety of covers, colors and profiles.* Installs in tile, stone, carpet, terrazzo, wood and polished concrete. Perfect for many applications, including schools, financial institutions, commercial office buildings, hospitality and residential.

Features & Benefits

One consistent design: Mix-and-match Resource RFBA Series Floor Boxes of any size with interchangeable components. Makes every project installation quick and efficient.

Improved wire and cable routing: Allows for easier wire pulling in adjacent compartments and around corners, reducing the overall cost for most cabling requirements.

Removable dividers post-pour: Fully adjustable before and after concrete pour.

Universal sized conduit feed: Meets all requirements for each box. 2- and 4-gang shallow boxes accept a 1" conduit feed, while all standard boxes accept a 2" conduit feed.

Two finishes: Every box configuration is available in either a standard zinc-plated construction or a lightweight "slab-on-grade" finish with fusion-bonded epoxy corrosion resistant paint.

Adapts to most power and communications needs: Common mounting plates can be used for any of the Resource RFB Series Floor Boxes. Reduces overall life cycle cost.

Specifications

General Info

| | | | |
|---------------------|-----------|-----------------------|--|
| Product Line | Wiremold | UPC Number | 786564105299 |
| Country Of Origin | Mexico | Installation Location | Above Grade |
| Number of Knockouts | 14 | Application Sector | Commercial |
| Standard | UL514 | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |
| Type | Floor Box | | |

Dimensions

| | | | |
|-------------------|----------|------------------|------------------------|
| Product Weight US | 11.78 lb | Product Depth US | 2.5 in |
| Product Length US | 17.75 in | Knockout Size | 1 in, 1-1/4 in, 3/4 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|------|--------------|-----|
| cULus ListingNumber | QCIT | cULus Listed | Yes |
|---------------------|------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | | | |
|-------------------------------|-----|---|-----|
| RoHS Compliant | Yes | Product Has Potential to Contribute to LEED | Yes |
| Product Environmental Profile | Yes | | |

Technical Information

| | | | |
|------------------------|---|----------------------------|--------|
| Floor Type | Carpet, Concrete, Polished Concrete, Tile, Wood | Service Capacity | Dual |
| Minimum Floor Depth | 2.5 in | Number of Gangs | 2 |
| Number of Compartments | 2 | Plenum | No |
| Box Capacity | 2 Gangs | Indoor/Outdoor | Indoor |
| Box Type | Above-Grade | Depth Behind Device Plates | 3 in |