



radiant Collection  
Discontinued - radiant® Incandescent 700W Dimmer, Dark Bronze  
Part No. RH703PDBCCV4



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with incandescent bulbs and fixtures. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

For use with incandescent bulbs and fixtures on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications. Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction. More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection. Screw pressure plate back wire allows easier installation and fit into the wall box

Eliminates the need to derate LED bulbs when in multi-gang situations. For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	RHCL453PDBCCV4
Color	Dark Bronze	Finish	Frosted
Country Of Origin	China	Switch Type	Paddle
Number of Switches	1	Package Quantity	1
Application Sector	Residential	Standard	cULus, CSA Listed, UL 1472

---

Warranty Type	Limited Lifetime Warranty	Type	Dimmer
---------------	---------------------------	------	--------

---

## Dimensions

---

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

---

## Technical Information

---

Preset	Single-Pole or 3-Way	Compatibility	Incandescent Load 700W or less
Frequency Rating	60 Hz	Connection	Screw-down terminals
Number of Gangs	1	Amperage	15 A
Bulb Compatibility	Incandescent	Number of Poles	3-Way, Single Pole
Indoor/Outdoor	Indoor	Wattage	700 W
Mounting Type	Box	Supply Voltage	120 VAC
Voltage	120.0 V	Environmental Conditions	95% (relative humidity, non-condensing)

---