radiant Collection

radiant® Incandescent 700W 3-Way Dimmer, Tri-Color

Part No. RH703PTCCCV6

Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant Registered Collection is optimized for use with incandescent bulbs and fixtures. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

For use with incandescent bulbs and fixtures on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Screw pressure plate back wire allows easier installation and fit into the wall box

Eliminates the need to derate LED bulbs when in multi-gang situations

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Satin	UPC Number	785007053715
Country Of Origin	China	Material	Polycarbonate
Product Type	Dimmer, Wall Switch	Features	Color Change Kit, Locator Light, Low-End Trim (Dim Range)
Switch Type	Paddle, Slider	Number of Switches	1

Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Technical Information

Load Rating	120V 700W (Halogen), 120V 700W (Incandescent)	Dimming Compatibility	Forward Phase
Frequency Rating	60 Hz	Maximum Humidity	95% (relative humidity, non-condensing)
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Wattage	700 W	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	Halogen, Incandescent		