



radiant Collection
radiant® Tru-Universal Single Pole/3-Way Dimmer, Tri-Color
Part No. RH703PTUTC



Upgrade your space with superior dimming control and exceptional style. The radiant® Tru-Universal Dimmer works with virtually any 120V dimmable bulb or fixture, adjusting to the precise light level you want, without the flicker. Unsure what dimmer your bulb needs? Avoid uncertainty with Tru-Universal Dimming. Part of the radiant® Collection, it also features clean lines and smooth control for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Works with virtually any 120V dimmable bulb or fixture on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level when turning back on or after a power outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating* required in multi-gang applications. *Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Matte	UPC Number	785007053470

Country Of Origin	China	Features	Auto-Calibration (Trim), High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)
Switch Type	Paddle, Single Pole 3-Way, Slider	Number of Switches	1
Application Sector	Residential	Standard	CSA Listed, cULus, UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer
Dimensions			
Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 5.5A (EFL), 120V 500VA (MLV), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent)	Dimming Compatibility	Forward or Reverse Selectable Phase
Frequency Rating	60 Hz	Connection	Screw Terminals
Number of Gangs	1	Minimum Load Recommendation	6 W
Amperage	15 A	Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon

Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Trim/Adjustment Level	Button	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Environmental Conditions	Humidity: Less than 95% non condensing		