



radiant Collection  
radiant® 120V, 700VA, Magnetic Low-Voltage Single Pole/3-Way Dimmer, White  
Part No. RHLV703PW



Upgrade your space with precise dimming control and exceptional style, while saving energy and extending bulb life by reducing the amount of electricity required to power the lights. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Usable in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                              |                    |                           |
|--------------------|------------------------------|--------------------|---------------------------|
| Product Line       | Pass & Seymour               | Color              | White                     |
| Country Of Origin  | China                        | Switch Type        | Paddle                    |
| Number of Switches | 1                            | Application Sector | Residential               |
| Standard           | CSA Listed, cULus, UL Listed | Warranty Type      | Limited Lifetime Warranty |
| Type               | Dimmer                       |                    |                           |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.75 in | Product Depth US | 1.25 in |
|------------------|---------|------------------|---------|

---

Product Height US      4.25 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed      Yes

---

### Technical Information

---

|                  |              |            |                 |
|------------------|--------------|------------|-----------------|
| Frequency Rating | 120VAC 60 Hz | Connection | Screw Terminals |
|------------------|--------------|------------|-----------------|

---

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

---

|                    |         |                 |                    |
|--------------------|---------|-----------------|--------------------|
| Bulb Compatibility | Halogen | Number of Poles | 3-Way, Single Pole |
|--------------------|---------|-----------------|--------------------|

---

|         |       |               |     |
|---------|-------|---------------|-----|
| Wattage | 700 W | Mounting Type | Box |
|---------|-------|---------------|-----|

---

|         |         |      |             |
|---------|---------|------|-------------|
| Voltage | 120.0 V | Load | Low Voltage |
|---------|---------|------|-------------|

---

|                          |  |  |  |
|--------------------------|--|--|--|
| Environmental Conditions | Humidity: Less than 95% non condensing |  |  |
|--------------------------|--|--|--|

---