

60As HP Replacement Switch with Auxiliary Contact



Features & Benefits

With Auxiliary Contact

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
Finish	Matte	UPC Number	785007133844
Country Of Origin	United States	Material	VALOX
Features	Replacement Part	Application Sector	Industrial
Type	Replacement Switch		

Dimensions

Product Width US	7.3 in	Product Depth US	7.1 in
Product Height US	11.6 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Horsepower Rating	15 HP @ 3Ø 240 VAC, 15 HP @ 480 VAC, 15 HP @ 600 VAC, 3 HP @ 120 VAC, 30 HP @ 3Ø 480 VAC, 30 HP @ 3Ø 600 VAC, 7-1/2 HP @ 240 VAC, 7-1/2 HP @ 277 VAC	Terminal Accommodation	#14 AWG - #10 AWG
Connection	Hardwired	Amperage	60 A
Enclosure Type	Not included.	Maximum Horsepower Rating	30 HP @ 3Ø 600VAC
Voltage	120 to 600 V		