



Wattstopper
Astronomic Time Switch 24/7 800W, Ivory, Box
Part No. RT-200-I



The RT-200 Astronomical time clock and timer switch automatically turns lighting or other loads on and off according to user programming. It replaces standard single-pole wall switches for energy savings and security.

Features & Benefits

Turns lights on and off relative to dusk or dawn, or at selected times of day on selected days of the week

Bright OLED display for clear viewing from a wide angle

Shipped in default 2 hour countdown time, easily changed to other lengths or none.

Ideal for any application where precise time-based control is desired

Includes eight programmable control schedules

Ideal for meeting California Title 24 Residential Exterior Astronomical Time-Switch with max 6 hour countdown requirement

Ideal for meeting California Title 24 Residential Exterior Astronomical Time-Switch with max 6 hour countdown requirement

Specifications

General Info

| | | | |
|--------------------|-----------------------|-------------------|--------|
| Product Line | Wattstopper | Color | Ivory |
| UPC Number | 754182918485 | Country Of Origin | China |
| Features | Single Display, Timer | Switch Type | Push |
| Application Sector | Commercial | Warranty Type | 5-Year |

Dimensions

| | | | |
|-------------------|-------------|-------------------|---------|
| Product Width US | 2.0 in | Product Weight US | 0.35 lb |
| Product Volume US | 27.84 cu in | Product Depth US | 4.5 in |

| | |
|-------------------|---------|
| Product Height US | 2.25 in |
|-------------------|---------|

Additional Information

| | | | |
|-----------------|-----|--|-----|
| RoHS Conformant | Yes | DesignLights Consortium Qualified System | Yes |
|-----------------|-----|--|-----|

| | |
|----------|-----|
| Security | Yes |
|----------|-----|

Technical Information

| | | | |
|-------------------|---|----------|-------|
| Number of Buttons | 1 | Amperage | 4.3 A |
|-------------------|---|----------|-------|

| | | | |
|--------------|----------------------|---------|--------|
| Timing Range | 24-Hour Programmable | Wattage | 1200 W |
|--------------|----------------------|---------|--------|

| | | | |
|---------|-----------|-----------------|-------|
| Voltage | 120/277 V | Connection Type | Wired |
|---------|-----------|-----------------|-------|