



radiant Collection  
radiant® 4-Button Digital Timer, Ivory  
Part No. RT2I



Installs easily in place of a standard light or fan switch, or older spring-wound timer and includes manual on/off through the paddle switch for added convenience. A locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Works with a variety of light bulbs or fixtures, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Automates control of lights for energy and cost savings. Also includes manual on/off through the paddle switch for added convenience.

Lets you select a desired preset shut-off time, including 60, 40, 20 and 10 minutes.

Installs easily in place of a standard light or fan switch, or older spring-wound timer.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                        |                    |        |
|--------------------|------------------------|--------------------|--------|
| Product Line       | Pass & Seymour         | Color              | Ivory  |
| Country Of Origin  | China                  | Features           | Timer  |
| Switch Type        | Paddle                 | Number of Switches | 1      |
| Application Sector | Residential/Commercial | Standard           | cULus  |
| Warranty Type      | 5-Year                 | Type               | Switch |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.69 in | Product Depth US | 1.88 in |
|------------------|---------|------------------|---------|

Product Height US3.281 in

Technical Information

|                   |                   |                 |               |
|-------------------|-------------------|-----------------|---------------|
| Connection        | Back & Side Wired | Coil Voltage    | 120 V         |
| Contact Rating    | 600Watts          | Number of Gangs | 1             |
| Number of Buttons | 4                 | Amperage        | 15 A          |
| Action            | Single Pole       | Number of Poles | Single Pole   |
| Indoor/Outdoor    | Indoor            | Timing Range    | 10-60 minutes |
| Wattage           | 600 W             | Mounting Type   | Box           |
| Voltage           | 120.0 V           |                 |               |