




radiant Collection
radiant® 4-Button Digital Timer, White
Part No. RT2WCCV4



Installs easily in place of a standard light or fan switch, or older spring-wound timer and includes manual on/off through the paddle switch for added convenience. A locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Works with a variety of light bulbs or fixtures, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Automates control of lights for energy and cost savings. Also includes manual on/off through the paddle switch for added convenience.

Lets you select a desired preset shut-off time, including 60, 40, 20 and 10 minutes.

Installs easily in place of a standard light or fan switch, or older spring-wound timer.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|--------------------|------------------------|--------------------|--------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Features | Timer |
| Switch Type | Paddle | Number of Switches | 1 |
| Application Sector | Residential/Commercial | Warranty Type | 5-Year |
| Type | Switch | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.69 in | Product Depth US | 1.88 in |
|------------------|---------|------------------|---------|

Product Height US 4.2 in

Technical Information

| | | | |
|-----------------|---------|-------------------|---------------|
| Number of Gangs | 1 | Number of Buttons | 4 |
| Amperage | 15 A | Number of Poles | Single Pole |
| Indoor/Outdoor | Indoor | Timing Range | 10-60 minutes |
| Voltage | 120.0 V | | |
