



Features & Benefits

Occupancy-based control plus multi-way operation.
California Title 24 compliant.

Replaces 3-way or 4-way switches when used with
other RW3U603 sensors.

Lighted switch for visibility in darkened rooms.

Adjustable light level setting of 10 to 150 fc (100 to 1500
lux). Coverage: 180 degrees, max. 600 ft.2 (56m2).

For covering patents, see www.legrand.us/patents.

Two or more RW3U603 sensors connected together will allow
enhanced coverage of the controlled space.

Adjustable time delay of 15 seconds, 5, 15, 30 minutes.

Manual-ON operation.

Load: Incandescent, Fluorescent, Compact Fluorescent (CFL),
Magnetic Low-Voltage (MLV) and Electronic Low-Voltage (ELV) 1/6 hp.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	CH-250-LA
Country Of Origin	China		

Technical Information

Sensor Type	Occupancy, Vacancy	Voltage	120.0 V
-------------	--------------------	---------	---------