



Designed to replace a standard light or fan single pole switch, this vacancy sensor controls most types of lighting and is Ideal for bedrooms and baths.

Features & Benefits

California Title 24 compliant. .	Lighted switch for visibility in darkened rooms.
Manual-ON operation.	Fixed 30-minute time delay, no adjustment necessary.
Low-profile styling with uniform color-matched lens and device.	Coverage: 180 degrees, max. 600 ft.2 (56m2).
Load: Incandescent.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	RRW600VTC
Color	White	Country Of Origin	China
Application Sector	Residential	Standard	UL Listed
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	100000	Sensor Type	Vacancy
Voltage	120 V	Load	500 Watt