



4-inch Round Ceiling Box with J-Bracket, Two captive Mounting Nails and Four Auto/Clamps. 50 pack.

Features & Benefits

Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.

UL Listed for fan and fixture support.

For covering patents, see www.legrand.us/patents.

: Auto/Clamp cable clamps molded in, hold wire securely in box.

Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.

Specifications

General Info

| | | | |
|-----------------------|-------------------------|---------------------|--|
| Product Line | Pass & Seymour | Color | Black |
| UPC Number | 785007206951 | Country Of Origin | United States |
| Material | Thermoplastic | Features | Auto Clamps, Dual Threaded Mounting Holes, Fixture Rated |
| Installation Location | Ceiling | Number of Knockouts | 4 |
| Application Sector | Commercial, Residential | Standard | UL listed |
| Warranty Type | 1-Year Limited Warranty | Type | Ceiling Box |

Dimensions

| | | | |
|------------------|--------|-------------------|---------|
| Product Width US | 4.0 in | Product Weight US | 0.36 lb |
|------------------|--------|-------------------|---------|

| | | | |
|-------------------|-------------|------------------|----------|
| Product Volume US | 20.25 cu in | Product Depth US | 2.188 in |
|-------------------|-------------|------------------|----------|

| | |
|----------------|-----------------------|
| Cubic Capacity | 20.25 in ³ |
|----------------|-----------------------|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|----------------|--------|-------------|------------|
| Indoor/Outdoor | Indoor | Cable Entry | Back, Side |
|----------------|--------|-------------|------------|

| | | | |
|-----------|-------|---------------|------------|
| Box Shape | Round | Mounting Type | Stud Mount |
|-----------|-------|---------------|------------|
