



Pass and Seymour  
4-in Round Ceiling Boxes  
Part No. S120RGAC



4 Inch Round Ceiling Box With Threaded Mounting Holes and Ground Lug Auto/Clamps 50 Pack

## Features & Benefits

Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.

UL Listed for fan and fixture support.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

: Auto/Clamp cable clamps molded in, hold wire securely in box.

Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007206982	Country Of Origin	United States
Material	Thermoplastic	Features	Auto Clamps, Dual Threaded Mounting Holes, Fixture Rated
Installation Location	Ceiling	Number of Knockouts	4
Application Sector	Commercial, Residential	Standard	UL listed
Warranty Type	1-Year Limited Warranty	Type	Ceiling Box, Ground Lug

### Dimensions

Product Width US	4.0 in	Product Weight US	0.25 lb
------------------	--------	-------------------	---------

---

Product Volume US	20.25 cu in	Product Depth US	2.188 in
-------------------	-------------	------------------	----------

---

Cubic Capacity	20.25 in <sup>3</sup>
----------------	-----------------------

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Indoor/Outdoor	Indoor	Cable Entry	Back, Side
----------------	--------	-------------	------------

---

Box Shape	Round	Mounting Type	Stud Mount
-----------	-------	---------------	------------

---