



The Ivory Series II 180 degree module with one RJ25 adapter with 6P6C 110 punchdown is engineered to load in the front and remove from the front snapping into place for installation, and can be removed easily for future modifications. This module is compatible with all Series II plates, panels and boxes delivering a compact design for easy and consistent installations.

Features & Benefits

Easy lace IDC housing: Reduces wiring time. Rugged Series II footprint: Fits in all Series II faceplates and housings.

Specifications

General Info

Product Line	Ortronics	Color	Ivory
UPC Number	662875637394	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL Standard
Warranty Type	5-Year	Type	Jack

Technical Information

Operating Temperature Min	-10 °C	Category Performance Rating	Cat6
Compatibility	Series II	Storage Humidity	0-100% RH
Plating Specification	Gold	Operating Temperature Max	60 °C
Amperage	1.5 A	Connector Type	110
Wattage	100 W	Operating Humidity	0-90% RH (Non-Condensing)
Voltage	60.0 V	Storage Temperature	-40° - 60° C