



Pass and Seymour  
Non-NEMA 3 Wire Plug - Black Back, White Front Body  
Part No. S2348DF

Non-Nema Plug, 14amp 125-480V, IP20 Suitability Back Front Body



## Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6/6 shell material.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

New-design external cord grips provide visible assurance of safe and proper cord retention.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Double dovetail design provides superior protection against cord pull-out forces.

Rounded back contour reduces snags and hang-ups on the job site.

Visible stamped NEMA configuration and device rating.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		

### Dimensions

Product Width US	1.406 in	Product Length US	1.8 in
------------------	----------	-------------------	--------

### Technical Information

Phase	3	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 - 0 AWG	Voltage	125.0 V